

Philips Decoflood² BVP626

Mounting instructions

Instructions de montage

Montageanleitung

Montage Instruktie

Istruzioni di montaggio

Instrucciones de montaje

Instrucces de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja Kiinnitysohjeet

Montaj yonergesi

Οδηγίες τήξεσσηθηθX






Instrukcja montazu

Szerelési utasítások






Navod k montazi

bycnerwoz gi vjynf.e

Navod k montazi




COL- OUR										
BVP626	2700	RG1	●	●	7.5kg	+25°C	+35°C	-20°C		0.06m ²
BVP626	4000	RG1	●	●	7.5kg	+25°C	+35°C	-20°C		0.06m ²
BVP626	GR	RG2	●	●	7.5kg	+25°C	+35°C	-20°C	MAX	0.06m ²
BVP626	BL	RG2	●	●	7.5kg	+25°C	+35°C	-20°C	51.3	0.06m ²
BVP626	RD	RG2	●	●	7.5kg	+25°C	+35°C	-20°C		0.06m ²
BVP626	RGB	RG2	●	●	7.5kg	+25°C	+35°C	-20°C		0.06m ²
BVP626	TWH	RG2	●	●	7.5kg	+25°C	+35°C	-20°C		0.06m ²



Risk Group 2 :- CAUTION Retinal Blue Light : Do not stare at operating lamp, may be harmful to the eyes.

100 - 277V
50 - 60Hz

INRUSH CURRENT
35 A / 350 μs



Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud

Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte

12NC 4413 181 06581


Versiodate: 02 / 12

Data subject to change without notice

Printed in United Kingdom


www.philips.com/lighting

PHILIPS




17mm	34 Nm


2




3



4a



4b




5a




Ø 10-14mm
ISO 20bis

60±1

10-11mm






5b




D+ REF D-

DMX


D+ REF D-




6



7




8




T20	2,4 Nm
8mm	34 Nm


9



T20	2,4 Nm



Installation scheme



MAX. Luminaires :32
Max. Distance between controller
and last luminaire :300 m