

Philips Decoflood² BVP636 / BVP646


Mounting instructions

Instructions de montage
Montageanleitung
Montage Instruktie
Istruzioni di montaggio




Instrucciones de montaje
Instrucces de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja Kiinnitysohjeet
Montaj yonergesi
Οδηγίες τήξεσσηθηθX
Instrukcja montazu

Szerelési utasítások
Navod k montazi
bycnerwoz gi vjynf:e
Navod k montazi




BVP636	2700	RG1	0,7m	●	●	12.9kg	+25°C	+35°C	-20°C	MAX 51.3	0.1m2
BVP636	4000	RG1		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2
BVP636	GR	RG2		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2
BVP636	BL	RG2		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2
BVP636	RD	RG2		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2
BVP636	RGB	RG2		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2
BVP636	TWH	RG2		●	●	12.9kg	+25°C	+35°C	-20°C		0.1m2



Risk Group 2 :- CAUTION Retinal Blue Light : Do not stare at operating lamp, may be harmful to the eyes.


100 - 277V
50 - 60Hz

INRUSH CURRENT
35 A / 350 μs




Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud

Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte




1

2 x M10




2




2

3




3

4a





4

4b




5



5a




Ø 10-14mm
ISO 20 BIS





5b




Ø 10-14mm
ISO 20 BIS




6

DMX


D+ REF D-




D+ REF D-




6



7




8




T20	2,4 Nm
8mm	34 Nm

9



T20	2,4 Nm



Installation scheme

